



### **DESCRIPTION**

Many years of in-field experience have shown the necessity of more and more efficient controls on the contamination level of hydraulic fluids and fuels.

With this goal uppermost in its mind, and thanks to sophisticated design patterns and the use of cutting-edge materials and technologies, FAI FILTRI has engineered a complete series of spin-on filters, in different models and sizes, designed to meet a wide array of filtration and operating requirements, in order to allow a more effective control of contamination levels in hydraulic, lubricating, engine circuits, etc.

The CSP series of reinforced cartridges, provide a valid solution for filtration problems, granting their best performances when fitted into hydraulic drives, in presence of supercharged hydrostatic drives, earthworks machines, compressors, converters, hydraulic systems return or exhaust lines with pressure peaks up to **25 bar**.

The fundamental characteristic of these elements is the possibility, for any clogged filter, to be easily replaced, by a quick and clean procedure, condition that has to be considered of great importance in working contexts where highly deteriorated environmental conditions usually occur.

They can support flow rates up to 270 l/min and each element can be fitted with a by-pass valve.

Specifically, FAI FILTRI spin-on cartridges, equipped with new-generation "A" filtering media, can grant high standards of performance even in the hardest conditions.

"A" type elements with absolute filtration power of 3, 6, 10, 25 micron ( $\beta x \geq 200$ ), are formed by inorganic impregnated and resin bonded inert micro-fibers, supported upstream and downstream. The result is a very compact filtering core which ensures the resistance of the media itself to deformation, distortion and strain ,preventing any contaminants to get released, thus improving filtering performances and allowing contaminants to accumulate efficiently, also in the event of phenomena such as high differential pressure and water hammering derived from cold starts and discharge flow rates.

The above mentioned features make the FAI FILTRI spin-on filters consistent with the use of hydraulic, lubricating oils, fuels, glycol water, emulsions and most synthetic fluids.

## **TECHNICAL DATA**

#### **MATERIALS**

- Galvanized stamped plate flange
- □ Sinned and painted sheet steel vessel
- Perforated/drilled supporting pipes and galvanized steel end-caps

#### **CARTRIDGES PRESSURE VALUES**

Max operating pressure 25 bar for models CSP015÷070

20 bar for models CSP083÷090 - CSP300÷400

Impulse test in compliance with ISO 3724: from 0-25-0 bar 1Hz 50.000 min. cycles (CSP015÷070)

from 0-20-0 bar 1Hz 50.000 min. cycles (CSP300÷400)

#### **FILTERING ELEMENTS**

"P" 10 and 25 nominal micron

made of  $\beta x$  > 2impregnated


cellulose fibers

"A" 3, 6, 10, 16 and 25 absolute

 $\begin{array}{ll} \text{micron made of} & \beta x \ \geq \ 200 \\ \text{reinforced} & \text{inorganic} \\ \text{microfibers} & \text{with} & \text{polyester} \end{array}$ 

protections

New generation "A" filtering elements structure



#### **RETENTION POWER**

In compliance with ISO 4572 Multi-pass test method

Filter	Dimension for β (μm) Value				Filtering rapport			Final ∆P
element	β ≥ 2 50%	β ≥ 20 95%	β ≥ 75 98,7%	β ≥ 200 99,5%	$\beta_2$	β <sub>10</sub>	$\beta_{20}$	(bar)
A03	-	2	2.4	3	20	>10000	>10000	7
A06	-	3	4.6	6	8	>2000	>10000	7
A10	3	6	7.8	10	1.5	≥200	>1000	7
A16	7	9	12	16	-	>25	>5000	7
A25	13	19	22	25	-	>1.5	>35	7
P10	10	>30	>30	-	1	2	4.5	4
P25	25	>30	>30	-	1	1	1.3	4

#### INTERNATIONAL STANDARDS FOR FLUIDS CONTAMINATION CONTROL

ISO 4406 CONTAMINATION CODES		NAS 1638 CORRESPONDING CLASS	SUGGESTED FILTRATION	APPLICATION FIELDS	
5 μm 15 μm			βx ≥ <b>200</b>		
12	9	3	1-2	High accuracy servo-plants – laboratory	
15	11	6	3-6	Servo-plants – robotics – aeronautics	
16	13	7	10-12	High sensitivity plants – where high standards of	
18	14	9	12-15	operating reliability are required	
19	19 16 10		15-25	General plant engineering with limited reliability	
21	21 18 12		25-40	Low pressure plants – desultory services	

#### **TESTS CARRIED OUT ON FILTER ELEMENTS**

Differential collapsing pressure of the filtering elements tested in compliance with ISO 2941

"P" type5 bar"A" and "M" types10 bar

Resistance to axial deformation tested in compliance with ISO 3723

Manufacturing conformity and determination/assessment of the first bubble point in compliance with ISO 2942

#### **FILTERING SURFACES**

Type	P10/P25	A06/A10/A25	Type	P10/P25	A06/A10/A25
CSP - 12	2300 cm <sup>2</sup>	1370 cm <sup>2</sup>	CSP - 70	3960 cm <sup>2</sup>	2700 cm <sup>2</sup>
CSP - 15	2060 cm <sup>2</sup>	1325 cm <sup>2</sup>	CSP - 90	4900 cm <sup>2</sup>	2630 cm <sup>2</sup>
CSP - 20	1100 cm <sup>2</sup>	765 cm <sup>2</sup>	CSP - 300	6250 cm <sup>2</sup>	3580 cm <sup>2</sup>
CSP - 50	2440 cm <sup>2</sup>	1700 cm <sup>2</sup>	CSP - 350	9350 cm <sup>2</sup>	5440 cm <sup>2</sup>
CSP - 60	2930 cm <sup>2</sup>	2040 cm <sup>2</sup>	CSP - 400	13580 cm <sup>2</sup>	7900 cm <sup>2</sup>

#### **BY-PASS VALVES**

Type -3- setting 1,75 bar

Type -4- setting 2,5 bar

Type -5- setting 3,5 bar

#### **GASKETS**

Buna-N "A" type gaskets

Viton "V" type gaskets

#### **COUPLINGS**

For the different couplings see order forms

[Specifically on request – custom-made]

#### **OPERATING TEMPERATURES**

From -25°C up to +110°C

For different temperatures please contact our technical department

#### **FLOW RATE**

From 20 up to 190 l/min

Choose the cartridge according to the filtration and to the recommended pressure drop.

### PRESSURE DROP

Curves are applicable to mineral oil with a dynamic viscosity of 30 mm $^2$ /sec. (cSt).  $\Delta P$  changes along with the values of dynamic viscosity according to the following formulas:


① Dynamic viscosity variations ≤5


$$\Delta P = \frac{v1}{v} \Delta P$$


② Dynamic viscosity variations >5

$$\Delta P1 = \frac{\frac{v1}{v} + \sqrt{\frac{v1}{v}}}{2} \Delta P$$


In both formulas  $\Delta P$  stands for the pressure drop calculated on the curves,  $\mathbf{v}$  stands for the reference dynamic viscosity (30 mm<sup>2</sup>/sec);  $\Delta P1$  is the pressure drop to be calculated and  $\mathbf{v}1$  stands for the actual dynamic viscosity of the fluid tested.








# **DIMENSIONAL INFORMATION**



Туре	Flow rate [I/min]	Α	В	С	D	E
CSP 012	20	76	120			
CSP 015	20	76	140	ORDER CODE	62,5	71,5
CSP 020	25	96	95			
CSP 025	25		110			
CSP 050	35 42		148			
CSP 060			170			
CSP 070	55		210			
CSP 090	100	108	260	SEE	96,5	106,5
CSP 300	120		175		100,5	
CSP 350	150	138	230			109,5
CSP 400	190		310			

## **ORDER CODE**



Couplings							
	Type 12 ÷ 15	Type 20 ÷ 70	Type 90	Type 300 ÷ 400			
0		3/4" GAS		1 1/4" GAS			
1		3/4" - 16 UNF					
2	13/16" -						
3		1" - 12 UNF					
4		1"1/8 -					
6				1"1/2 - 16 UNF			
Α	M20x1,5						
В		M24x2					
С		M33x1,5					
D		M24x1,5					
Е	M18x1,5						
Н			M42x2				
Р			M30x2				